

# Leo<sup>®</sup>

Built for strength, designed for safety



Yes, you can.

## Explore with our compact and safety-assured scooter

The Invacare Leo® is a scooter designed for all those that value their independence and wish to get out and about unaided. Safety is a vital feature of the Leo®, but this does not detract from its stylish and sporty looks. Leo® offers users the freedom and confidence to enjoy their essential daily outings and leisure excursions. With exactly high standards of design and safety engineering, the Leo® undoubtedly sets a new market standard.



### For a safe, powerful drive

- ▶ The Invacare Leo® offers a smooth, safe drive in a scooter that is easy to control and manoeuvre. The Leo® intelligent lighting package includes indicators that automatically switch off and a rear brake light for safe driving. In addition to a visual warning for the battery level display, users are also alerted with an audible warning (beep) when the battery needs recharging.

### Compact

- ▶ The Leo® is a compact mini-scooter that can be easily dismantled for transportation during longer trips or weekend breaks. With a smooth drive and easy manoeuvrability, getting round tight corners in the local shopping centre, museum or leisure complex becomes refreshingly easy. Access to the battery and electronics for maintenance or servicing is much easier with the Leo® as only one part needs to be removed.

### Reliable

- ▶ Users can trust the Leo® to take them wherever they need to go. From a trip to the shops or a ride to the park, the Leo® is rendered sturdy and reliable thanks to its exceptionally high-quality electronic engineering and power. These elements are protected from corrosion and water (splash protection), which safeguard the vital workings of the scooter against dirt and moisture. A two-step disengaging lever protects the scooter from free-wheeling if inadvertently knocked out of drive mode. The lighting system is designed so that if one of the lights goes, all other lights continue to function.



## Features and Accessories



Finite tiller movement

Users can easily adjust the tiller to suit their needs.



Brake light

Rear brake lighting warns other people that the scooter is slowing down, thus preventing collisions.



Comfort seating

Swivel functionality and sliding rails ensure optimal seating position.



Two-step disengaging lever

This unique concept prevents the scooter from accidentally freewheeling.



Built in anti-splash guards

Protects electronics and the transaxle from dirt and water.



Disassembly into five parts

No tools are required to dismantle Invacare Leo.



Crutch & cane holder

Keeps your crutch or cane stable during the drive.



Lockable front box

Secure box for personal valuables.



Seatbelt

Keeps the user well-positioned in the seat.



Large mirror

Can be mounted left or right.



Heavy-duty storage cover

Keeps the scooter clean and dry.




Charging off-board

Simply remove batteries to charge with the off-board charger kit.



Seat suspension module

Adds extra comfort during driving.



Windscreen

Protects the user from the cold wind.

## Technical data

For more information about this product, including the user manual, please visit our website: [www.invacare.eu](http://www.invacare.eu)

				
	Backrest width ▼	Seat depth ▼	Seat to floor height ▼	Backrest height ▼
4 wheels	470 mm	410 mm	460 - 560 mm	475 mm
3 wheels	470 mm	410 mm	460 - 560 mm	475 mm

				
	Driving unit width ▼	Total length ▼	Empty weight ▼	Max. User weight ▼
4 wheels	590 mm	1220 mm	59 kg (excl. batteries) 83 kg (incl. batteries)	136 kg
3 wheels	590 mm	1200 mm	54 kg (excl. batteries) 78 kg (incl. batteries)	136 kg

				
	Battery capacity ▼	Turning diameter ▼	Max. Climbable obstacle height ▼	Ground clearance ▼
4 wheels	2 x 36 Ah	2620 mm	60 mm	70 mm
3 wheels	2 x 36 Ah	2320 mm	60 mm	70 mm

				
	Max. Safe slope ▼	Motor capacity ▼	Max. Driving distance ▼	Max. Driving speed ▼
4 wheels	10°	240 W	38 km	8 km/h
3 wheels	10° <sup>1</sup>	240 W	36 km	8 km/h

1. Seat in maximum fifth rearward locking position from the front.

### Shroud colours



Moonstone Silver



Onyx Blue



Ruby Red

### Upholstery



Black Vinyl